

## Product information

# 94 55 200

## Anvil shears

- Drawing cut against firm surface for cutting soft materials without damage, e.g. rubber profiles, PVC, leather, wood, hoses etc.
- Cuts flat material with a max. width of 40 mm and height of 7.5 mm
- Cutting capacity for round material up to Ø 25 mm
- Strong, replaceable blade
- With opening spring and locking device
- Tool body: tool steel, rolled, oil-hardened



AAA

General	
Article No.	94 55 200
EAN	4003773080763
Shears	chrome-plated
Handles	with plastic grips
Weight	290 g
Dimensions	200 x 75 x 22 mm
Reach	no
RohS	no
Technical details	
Blade length	40.0 mm
Classification	
eCl@ss 5.1.4	21040601
proficl@ss 6.0	AAA513c002
UNSPSC 13.1	23151901
Accessories	
94 59 200 01	Spare blade for 94 55 200,
94 59 200 02	Spare anvil for 94 55 200,
Spare Parts	
94 59 200 01	Spare blade for 94 55 200,

technical change and errors excepted



