

Product information

95 12 165 T

Cable Shears



- Pliers with tether attachment point for mounting a fall protection system
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



General

Article No.	95 12 165 T
EAN	4003773080190
Shears	burnished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	255 g
Dimensions	165 x 54 x 22 mm
Reach	no
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	50 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
Drop Protection System	yes

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable