

Product information

95 12 500

Cable Shears



- Short design, length only 500 mm
- Low weight, high leverage
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Low handforce required due to favourable lever ratio and special blade geometry
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Cutter head: vanadium electric steel, forged, oil-hardened
- Handles: aluminium tube, high-strength

General

Article No.	95 12 500
EAN	4003773069966
Head	burnished
Handles	with multi-component grips
Weight	1,090 g
Dimensions	500 x 160 x 35 mm
Reach	no
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	150 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 27 mm
AWG	6 / 0

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted

