

Product information

97 49 19

- Application: insulated + non-insulated wire ferrules 35 - 50 mm²

Crimping die


For wire ferrules



General

Article No.	97 49 19
EAN	4003773030898
Weight	46 g
Dimensions	50 x 12 mm
Reach	no
RohS	no

Technical details



Applications	insulated and non-insulated wire ferrules
Capacity in square millimetres	35 — 50 mm ²
Number of crimping positions	2
AWG	2 / 0

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820

technical change and errors excepted