

Product information

97 49 30

- Application: non-insulated crimp connectors in accordance with DIN 46267 1.5 - 4.0 and 6.0 + 10.0 mm²

Crimping die

For non-insulated butt connectors



General

Article No.	97 49 30
EAN	4003773030904
Weight	37 g
Dimensions	50 x 18 mm
Reach	no
RohS	no

Technical details



Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	1.5 — 4 mm ²
Number of crimping positions	5
AWG	16 — 8



Capacity in square millimetres	6 / 10 mm ²
Number of crimping positions	2
AWG	10 / 8



Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820

technical change and errors excepted