

Product information

97 52 30

KNIPEX PreciForce®
Crimping Pliers


- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened




General

Article No.	97 52 30
EAN	4003773051855
Pliers	burnished
Handles	with multi-component grips
Weight	477 g
Dimensions	220 x 70 x 31 mm
Reach	yes
RohS	no

Technical details



Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	1.5 — 10.0 mm ²
Number of crimping positions	5
AWG	16 — 12



Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	6.0 / 10.0 mm ²
Number of crimping positions	2
AWG	10 / 8

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts

97 59 20	Extension spring for 97 52 XX, small
----------	--------------------------------------



Spare Parts

97 59 21	Extension spring for 97 52 XX, large
97 59 20	Extension spring for 97 52 XX, small
97 59 21	Extension spring for 97 52 XX, large

technical change and errors excepted