

## Product information


# 97 52 34

## KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 52 34
EAN	4003773051879
Pliers	burnished
Handles	with multi-component grips
Weight	483 g
Dimensions	220 x 59 x 21 mm
Reach	yes
RohS	no

Technical details	
	
Applications	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 2.5 mm <sup>2</sup>
Number of crimping positions	4
AWG	26 — 14

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts	
97 59 20	Extension spring for 97 52 XX, small
97 59 21	Extension spring for 97 52 XX, large
97 59 20	Extension spring for 97 52 XX, small
97 59 21	Extension spring for 97 52 XX, large

technical change and errors excepted