

Product information


97 61 145 A

Crimping Pliers for wire ferrules

- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm²
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened



General	
Article No.	97 61 145 A
EAN	4003773035558
Head	polished
Handles	plastic coated
Weight	140 g
Dimensions	145 x 52 x 13 mm
Reach	no
RohS	no

Technical details	
	
Applications	Wire ferrules
Capacity in square millimetres	0.25 — 2.5 mm ²
Number of crimping positions	4
AWG	24 — 14

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted