

Digital multimeter up to 600 V AC, CAT IV incl. 2x AAA batteries (45218)

**wiha** 

Tools that work for you

Wiha Werkzeuge GmbH  
Obertalstraße 3-7 78136 Schonach  
E-Mail: info.de@wiha.com  
Tel.: +49 (0)7722 959-0



Order no.: 45218

Article number: SB25541

EAN: 4010995452186

Customs tariff number: 90303100

Increases your efficiency: All relevant measurement functions in a single measuring device.  
Makes handling easier: Automatic measuring range setting saves the manual pre-selection.  
Simplifies your work: Simplifies storage and relative value measurement and expedites the comparison of measured values.

Dimensions: 150 x 80 x 45 mm

Application: For multi-functional use in different application locations.

Measuring category: CAT III up to 600 V, CAT IV up to 300 V.

Standard: IP 40. CE and GS certified.

Are you looking for a multimeter that covers the relevant measurement variables needed during the workday of an electrician? The digital multimeter from Wiha optimally equips you for a wide variety of measurements. This single tool can be used to make voltage, current, resistance, frequency, capacity, and temperature measurements. In addition, continuity and diode tests are also possible. A large LCD display makes the measurement results immediately readable even beyond the measurement process. An additional signal sound indicates the current flow during the continuity check. Thanks to the automatic measuring range selection, the manual pre-selection of specific measurement ranges is no longer required. The relative value measurement offers another advantage. The storage of previous measurement values and their comparison to future measurement results allows a variety of control options. According to the measurement categories CAT III up to 600 V and CAT IV up to 300 V, the digital multimeter from Wiha offers maximum safety for working on building installations and directly on the sources of low-voltage installations.

EN 61010-1, EN 61010-2-033, EN 61010-031.

---

Customs tariff number

90303100

---

Blister pack	No
--------------	----

---

Overall length (mm)	150 mm
---------------------	--------

---

Country of origin (ISO 3166-1 Alpha 3)	CHN
--	-----

---

Weight PU in grams	640
--------------------	-----