



- Unique cradle design provides maximum stability for cable bundle
- Low profile design keeps bundle close to mounting surface where overhead space is limited

‡Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy Standard, LH = Light-Heavy

Part Number: TM3S25-C  
Product Family: Cable Tie Mounts  
Product Line: Screw Mounts

Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Cable Tie Mount - Screw Applied

Product Type: Cable Tie Mounts - Screw / Rivet Mounted

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Height (In.): .38

Height (mm):	9.5
Length (In.):	.86
Length (mm):	21.8
Width (In.):	.61
Width (mm):	15.5
CE Compliant:	CT-ACC2 / 10.96
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.26
Hole Diameter (mm):	6.6
Metric Screw Size:	M6
Mounting Method:	1/4 (M6) Screw
Screw Size:	1/4 (M6)
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I, S, LH
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100