



- Unique cradle design provides maximum stability for cable bundle
- Low profile design keeps bundle close to mounting surface where overhead space is limited

‡Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy Standard, LH = Light-Heavy

Part Number: TM3S10-C0
Product Family: Cable Tie Mounts
Product Line: Screw Mounts

Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Cable Tie Mount - Screw Applied

Material: Weather Resistant Nylon 6.6

Color: Black

UL Recognized: E136577

Height (In.): .38

Height (mm): 9.5

Length (In.):	.86
Length (mm):	21.8
Width (In.):	.61
Width (mm):	15.5
CE Compliant:	CT-ACC2 / 10.96
Environment:	Outdoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.19
Hole Diameter (mm):	5.0
Metric Screw Size:	M5
Mounting Method:	#10 (M5) Screw
Screw Size:	#10 (M5)
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I, S, LH
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100