

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Replacement battery, VRLA-AGM, 2x12 V DC, 4 Ah. Only for 1274117 UPS-BAT/PB/24DC/4AH, 2320267 QUINT-UPS/24DC/24DC/10/3.4AH from V/C 06, 2905908 TRIO-UPS-2G/1AC/1AC/120V/750VA, and 2905909 TRIO-UPS-2G/1AC/1AC/230V/750VA

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Commercial Data

Item number	1283116
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	CMUEV3
GTIN	4063151487676
Weight per Piece (including packing)	2,950.8 g
Weight per Piece (excluding packing)	2,950.8 g
Customs tariff number	85072080
Country of origin	CN

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Technical Data

Energy storage

Input voltage	2x 12 V
Nominal capacity	4 Ah
Accumulator module service life (according to Eurobat)	6 (20 °C)
Latest startup date (battery only)	6 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	3 Months ... 6 Months (20 °C ... 30 °C)
	1 Months ... 3 Months (30 °C ... 40 °C)
Battery type	BB Battery HR4.2-12FR
Battery technology	VRLA-AGM
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.

Product properties

Product type	Battery unit
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.

Insulation characteristics

Protection class	III
Degree of pollution	2

Dimensions

Width	82 mm
Height	142 mm
Depth	102 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (storage/transport)	-20 °C ... 40 °C
Ambient temperature (charge)	0 °C ... 40 °C
Ambient temperature (discharge)	-20 °C ... 50 °C
Max. permissible relative humidity (operation)	≤ 95 %

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Approvals



GOST-R

Approval ID: ROSS DE.BL08.D00191



EAC

Approval ID: RU*DE*01.B.78948/21

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Classifications

ECLASS

ECLASS-11.0

27059090

ETIM

ETIM 8.0

EC011878

UNSPSC

UNSPSC 21.0

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/4AH



1283116

<https://www.phoenixcontact.com/in/products/1283116>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 8 For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in