

CREALITY

MPN - CR-SCAN 01

Description – CR-Scan 01 3D Scanner Upgraded Combo



A bridge between reality and virtual reality, takes you into cyberspace.

- True Color
- No Marker Scanning
- One-click Model Optimization
- High Precision of 0.1mm and Ultra Large Format
- Handheld Mode and Turntable Mode, Flexible and Portable

Product Parameters

Flame Rate: 10fps

Single Frame Scan Range: 536*378 mm

Accuracy: 0.1 mm

Spatial Resolution: 0.5 mm

Scanning Distance: 400mm-900mm

Scanning Range (Handheld) : 0.3m-2m

Scanning Range (Turntable) : 0.3m-0.5m

Output Format: obj / stl

Data Interface: USB 3.0

Operating Temperature: 0-40°C

Compatible System: WIN 10 64BIT / Mac OS

Minimum Computer Configuration Requirements: 8G RAM above and 2G graphics card memory above