

FGG.0T.305.CLAC45Z

SUMMARY

Wires

Low voltage 5



Image is for illustrative purpose only

Series 0T

Termination type Male solder

IP rating 68

AWG wire size 30.00 - 22.00

Cable Ø 4.10 - 4.50 mm

Status active

Matching parts EGG.0T.305.CLL

Download

Request a quote

Eplan Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model FG*: Straight plug, cable collet and nut for fitting a bend relief

Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Variant Z: Nut for fitting a bend relief

Weight 8.24 g

Performance

Configuration T.305: 5 Low Voltage

Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 6.5 Amps

Specifications

Contact Type: Solder

Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in)

Max. Stranded Conductor: 0.34 mm² (AWG 22)

Max. Conductor: 0.34 mm² (AWG 22)

R (max): 6.1 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 700 V (AC), 1000 V (DC) Vtest (contact-contact): 1000 V (AC), 1400 V (DC)

Others

Endurance (Shell): >3000 mating cycles Temp (min / max): -55°C / +200°C


Humidity (max): <=95% [at 60 deg C /140 F] Resistance to vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21

Shielding efficiency (min): 75 dB (at 10 MHz) Shielding efficiency (min): 40 dB (at 1 GHz)

Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	А	L	М	S1	S2
mm.	9.5	38	28	7.5	7
in.	0,37	1,50	1,10	0,30	0,28

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

50090	DVC	Black	
30070	1 1 0	Dlack	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.