



Sample photo

Order symbol: CAB PC 403018 G3B
Product nbr: 8113352
Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020246
El. number:
Finland: 3424118
Electric No. Denmark: 8212019247
Electric No. Italy: 7821045
Electric No. Sweden: 2539975

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height
mm:	400	300	180
inch:	15.7	11.8	7.1

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:	
EKIV 43	Mounting plate

Accessories:	
EKIV 43 PL	Mounting plate, Plastic
EKIV 27	DIN-35 Mounting rail
DS35270E1	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 43	Front plate
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set

Rating:
Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:
SGS Fimko
Gost R

