

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150310433](#)
Status: **Active**
Overview:
Description: 0.30mm Pitch Premo-Flex FPC Jumper with Notches, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 33 Circuits

General

Product Family	Cable
Series	15031
Crimp Quality Equipment	Yes
Overview	premo-flex
Product Name	Premo-Flex FFC Jumper
UPC	195842786738

Physical

Cable Length	102.00mm
Circuits (Loaded)	33
Circuits (maximum)	33
Contact Layout Type	A (same side)
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.30mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flexible Printed Circuitry

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Material Info

Reference - Drawing Numbers

Product Specification	150310001-000
Sales Drawing	150310001-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[15031](#) Series

Mates With

Easy-On FPC Connector [5047543300](#)