



Pushing Performance
Since 1945

Han TC70-HMC-FC-CRT-10mm²-AU



Part number	09 11 200 6231
Specification	Han TC70-HMC-FC-CRT-10mm ² -AU
HARTING eCatalogue	https://b2b.harting.com/09112006231

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact
Features	lead-free

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	10 mm ²
Operating current	≤70 A
Contact resistance	≤0.3 mΩ
Stripping length	15.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	10
Net weight	7.1 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors