


hood

VMPAL-KM-SD25-IP67-0

Part number: 560428

FESTO



Data sheet

Feature	Value
Product weight	100 g
Electrical connection	pre-assembled
Permissible cable diameter	5 ... 13 mm
Terminal cross-section	0.2 ... 0.5 mm ²
Protection class	IP67 to IEC 60529
Ambient temperature	-5 ... 80 °C
CE mark (see declaration of conformity)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B1/B2-L
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress