



01080806

## Aluminium Enclosure Standard

80 x 75 x 57 mm

Aluminium Enclosure Standard 80 x 75 x 57 mm

[Catalogues](#)
[Declaration of Conformity](#)
[Drawing](#)
[3D Data](#)
[Assignmentplan](#)
[Terminal Mounting](#)

## Technical data

Height	80 mm
Width	75 mm
Depth	57 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AISI 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-40 °C
temperature max.	90 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	TRUE
Approvals	Lloyd Register, Maritime Register, UL 508A

## Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tariff number	85369095
Weight	0.326
GTIN	4250157900081

## ETIM classification

ETIM 8	EC000058
--------	----------

## Accessories



**10011001**

Mounting plate for 01.080806



**10061003**

DIN rail 15 for 01.080806