

600V FAST ACTING FUSES

HCLR Series



- Fast Acting 600V Fuse
- Compact Design
- High Interrupt Rating
- 0.5 to 30 A Rating
- Class CC Fuse

A fast acting, high-interrupt capacity, current limiting type fuse. The HCLR style fuse provides an excellent choice for applications such as: lighting and resistive heating loads.

SPECIFICATIONS

Dimensions: 1/2" ferrule, 38 mm (1.5") length

Weight: Approx 3.2 oz (0.2 lb)

Voltage Rating: HCLR-600 Vac

Ampere Rating: 0.1 to 30 A

Interrupting Rating: 200k RMS Amps

Current Limiting: Class CC Fuse

Agency Approvals: UL Listed, Class CC, Guide JDDZ, File E162363; CSA Certified HCLR-MISC per C22.2, No.248.4



HCLR5 shown actual size.

To Order			
MODEL NO.	AMPERAGE	MODEL NO.	AMPERAGE
HCLR.5	0.5	HCLR6	6
HCLR.75	0.75	HCLR7	7
HCLR1	1.0	HCLR8	8
HCLR1.5	1.5	HCLR9	9
HCLR2	2.0	HCLR10	10
HCLR2.5	2.5	HCLR12	12
HCLR3	3.0	HCLR15	15
HCLR3.5	3.5	HCLR20	20
HCLR4	4.0	HCLR25	25
HCLR5	5.0	HCLR30	30

Ordering Examples: HCLR5, 600V fast acting fuse with 5 A rating.

HCLR.75, 600V fast acting fuse with 0.75 A rating.