

Product data sheet

Specifications



Wall-Mounted Open Box 9U W600 D600 Fixed 19" Glazed Door R7035

NSYOPB9U6F

Main

Range	Actassi
Product name	Actassi OPB
Product or component type	19" enclosure
Device application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure type	Open box
Support equipment	2 x fixed 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Glazed door
Door type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Side Rear Front
Removable parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless
Colour	Light grey (RAL 7035)

Complementary

Device composition	3 x cable entries 1 x glazed door front 2 x panels side 2 x 19" uprights front 1 x open structure
Load rating	50 kg static 3 kg by unit
Back face	Cut-out
Side face	Panel
Number of cut-out	1 cut-outside 1 cut-outbottom 1 cut-outtop
Installation mode	Wall mounted
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright

Surface finish	Epoxy-polyester powder
Width	600 mm
Height	515 mm
Depth	600 mm
Net weight	23.84 kg
Number of rack unit	9U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	IEC 60297-3-100 EIA-310D

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	23.84 kg
Package 1 Height	58.0 cm
Package 1 width	61.5 cm
Package 1 Length	65.0 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Weight	156.0 kg
Package 2 Height	182.0 cm
Package 2 width	80.0 cm
Package 2 Length	122.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------