

Product data sheet

Specifications



Wall-Mounted Open Box 18U W600 D500 Fixed 19" Plain Door R7035

NSYOPB18U5FR

Main

Range	Actassi
Product name	Actassi OPB
Product or component type	19" enclosure
Device application	Cabling
Applications	To improve security of the equipment To mount 19" equipment To protect network connectivity equipment
Enclosure type	Open box
Support equipment	2 x fixed 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Plain door
Door type	Front plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Side Rear Front
Removable parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless
Colour	Light grey (RAL 7035)

Complementary

Device composition	3 x cable entries 2 x panels side 2 x 19" uprights front 1 x open structure 1 x plain door front
Load rating	50 kg static 3 kg by unit
Back face	Cut-out
Side face	Panel
Number of cut-out	1 cut-outside 1 cut-outbottom 1 cut-outtop
Installation mode	Wall mounted
Material	Sheet steel: structure Sheet steel: door Galvanized steel: upright

Surface finish	Epoxy-polyester powder
Width	600 mm
Height	915 mm
Depth	500 mm
Net weight	30.25 kg
Number of rack unit	18U
Targeted region	Europe

Environment

IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	30.25 kg
Package 1 Height	55.0 cm
Package 1 width	61.5 cm
Package 1 Length	97.5 cm
Unit Type of Package 2	P12
Number of Units in Package 2	2
Package 2 Weight	65.0 kg
Package 2 Height	120.0 cm
Package 2 width	80.0 cm
Package 2 Length	120.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------