



Click [here](#) for the 3D model.

### Dimensions

D	22mm +1mm
L	30mm +2mm
S	10mm +/-0.5mm
LL	4mm +/-1mm
F	1.5mm +/-0.1mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400

### General Information

Series	ELH
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

### Specifications

Capacitance	100 uF
Capacitance Tolerance	20%
Voltage DC	450 VDC, 500 VDC (Surge)
Temperature Range	-25/+85°C
Rated Temperature	85°C
Life	2000 Hrs
Dissipation Factor	20% 120Hz 20C
Ripple Current	0.85 Amps (120Hz 85C)
Leakage Current	0.9 mA (5min 20°C)