

TE Internal #: 2063530-1  
 Hand Crimping Tools, Commercial Crimp Tooling, Operator  
 Releasable & Adjustable, Removable/Interchangeable, TE Product  
 Specification (114-), Manual

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**  
 Ratchet Configuration: **Operator Releasable & Adjustable**  
 Die Sets Type: **Removable/Interchangeable**  
 Specification Type: **TE Product Specification (114-)**  
 TE Certification: **Cannot be Certified**

### Features

#### Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	SDE Crimp Hand Tool

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-M8793-T273  
MQS, RECEPTACLE AND TAB



TE Part # 2063530-2  
SDE MQS 0.5-0.75mm2 DIE SET



TE Part # 5-965907-1  
MQS SOCKET CONTACT LOOSE PIECE



TE Part # 7-965908-2  
MQS0,63 Au tab LL EDS 0,5-0,75



TE Part # 5-965907-5  
MQS SOCKET CONTACT SWS



TE Part # 7-965906-5  
MQS0,63 Au rec LL EDS 0,5-0,75




TE Part # 965909-1  
MQS PIN CONTACT SWS



TE Part # 965909-2  
MQS PIN CONTACT SWS



TE Part # 1-965909-3  
MQS STIFT-KONT EDS



TE Part # 2-965909-2  
LP MQS PIN EDS SANTOVAC



TE Part # 2362810-1  
SDE CRIMP HAND TOOL FRAME W /O DIES



TE Part # 5-965908-3  
MQS0,63 Ag tab LL EDS 0,5-0,75



## Documents

### Datasheets & Catalog Pages

#### CRIMPING TERMINALS

English

#### CRIMPING WHERE FORM MEETS FUNCTION

English

#### Bottoming Dies

English

#### SDE Crimp Commercial Tool System

English

---

### Instruction Sheets

#### Instruction Sheet (U.S.)

English