

www.lemo.com

# PHG.2B.302.CLLD92Z

## **SUMMARY**

#### # Wires

Low voltage 2



Image is for illustrative purpose only

Series 2B

Termination type Female solder

IP rating 50

AWG wire size 22.00 - 14.00

Cable Ø 8.30 - 9.20 mm

**Status** active

Matching parts FGG.2B.302.CLAD92Z

### **Download**

Request a quote

Eplan Catalog

## **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model PH\*: Free receptacle, cable collet and nut for fitting a bend relief

**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Variant Z: Nut for fitting a bend relief

Weight 37.73 g

### **Performance**

Configuration 2B.302 : 2 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 25 Amps

## **Specifications**

Contact Type: Solder

Contact Dia.: 2 mm (0.079in) Bucket Dia.: 1.8 mm (0.071in)

Max. Solid Conductor: 1.5 mm<sup>2</sup> (AWG 14) Max. Stranded Conductor: 1.5 mm<sup>2</sup> (AWG 16)

R (max): 3.3 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 1750 V (AC), 2500 V (DC) Vtest (contact-contact): 2100 V (AC), 2970 V (DC)

## **Others**


Endurance (Shell): 5000

Temp (min / max):  $-55^{\circ}$ C /  $+250^{\circ}$ C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

# **DRAWINGS**



## **Dimensions**

	А	L	S1	S2
mm.	16.5	46	13	12
in.	0,65	1,81	0,51	0,47

## **RECOMMENDED BY LEMO**

## **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Spanner wrench: DCD.2B.ZZZ.PA120