

# Han 3A HMC-Base angled-M20



Image is for illustration purposes only. Please refer to product description.

	1000000	ADRINGSHED SETTON SETTEMENT		
TATAL PROPERTY AND ADDRESS OF THE PARTY OF T				
433300000000000000000000000000000000000	100000000000000000000000000000000000000	100000000000000000000000000000000000000		
NAME OF TAXABLE PARTY OF TAXABLE PARTY.	A SHOULD FOR	12011 100 100 100 100 100 100 100 100 10		
AND		A STANDARD CONTROL WAS A STANDARD CONTROL OF THE STAND		
	1 THE R. P. LEWIS CO., LANSING, MICH.	ESS 24 VO SERVICE DE LA SERVIC		

Part number 19 20 203 1160 Han 3A HMC-Base angled-M20 Specification HARTING eCatalogue https://b2b.harting.com/19202031160

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HMC
Type of hood/housing	Screw mounted housing
Description of hood/housing	Angled

#### Version

Size	3 A
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Special hoods and housings for high mating cycles
Details	$\mathrm{Han}^{\circledR}$ 3 A HMC housings shall only be combined with housings from the $\mathrm{Han}^{\circledR}$ 3 A HMC portfolio.

#### Technical characteristics

Limiting temperature	-40 +125 °C
Mating cycles with other HMC components	≥10,000
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)

Page 1 / 2 | Creation date 2022-10-08 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



## Material properties

Material (locking) Steel

Surface (locking) Zinc plated

## Specifications and approvals

Approvais DNV GL	Approvals	DNV GL	
------------------	-----------	--------	--

#### Commercial data

Packaging size	10
Net weight	94.3 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170742
eCl@ss	27440202 Shell for industrial connectors