

Han 3A HMC hood TE M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 203 1445
Specification	Han 3A HMC hood TE M25
HARTING eCatalogue	https://b2b.harting.com/19202031445

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] HMC
Type of hood/housing	Hood

Version

Size	3 A
Version	Top entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Special hoods and housings for high mating cycles
Details	Han [®] 3 A HMC housings shall only be combined with housings from the Han [®] 3 A HMC portfolio.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



Pushing Performance
Since 1945

Material properties

Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	77.9 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170728
eCl@ss	27440202 Shell for industrial connectors