

## Han 3A hood HMC



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 203 1440
Specification	Han 3A hood HMC
HARTING eCatalogue	<a href="https://b2b.harting.com/19202031440">https://b2b.harting.com/19202031440</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HMC
Type of hood/housing	Hood

### Version

Size	3 A
Version	Top entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Special hoods and housings for high mating cycles
Details	Han <sup>®</sup> 3 A HMC housings shall only be combined with housings from the Han <sup>®</sup> 3 A HMC portfolio.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



**Pushing Performance**  
Since 1945

## Material properties

Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	64.3 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170704
eCl@ss	27440202 Shell for industrial connectors