

## Han 3A HMC Housing



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 20 203 0301  |
| Specification      | Han 3A HMC Housing  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09202030301">https://b2b.harting.com/09202030301</a> |

### Identification

|                             |                          |
|-----------------------------|--------------------------|
| Category                    | Hoods/Housings           |
| Series of hoods/housings    | Han <sup>®</sup> HMC     |
| Type of hood/housing        | Bulkhead mounted housing |
| Description of hood/housing | Straight                 |

### Version

|                      |   |
|----------------------|---|
| Size                 | 3 A   |
| Locking type         | Single locking lever  |
| Field of application | Special hoods and housings for high mating cycles   |
| Details              | Han <sup>®</sup> 3 A HMC housings shall only be combined with housings from the Han <sup>®</sup> 3 A HMC portfolio. |

### Technical characteristics

|   |  |
|---|--|
| Limiting temperature                    | -40 ... +125 °C                                    |
| Mating cycles with other HMC components | ≥10,000  |
| Degree of protection acc. to IEC 60529  | IP44<br>IP65 / IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E      | 12   |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast        |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 7037 (dust grey) |
| Material (seal)         | NBR                  |



**Pushing Performance**  
Since 1945

## Material properties

|                    |             |
|--------------------|-------------|
| Material (locking) | Steel       |
| Surface (locking)  | Zinc plated |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 10                                       |
| Net weight                     | 29 g                                     |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140170759                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |