




## Datasheet

## IEC PTFE Insulated Flat Pair Thermocouple Extension Cable



- PTFE insulated flat pair cable
- Single pair of PTFE insulated conductors, laid flat with PTFE jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilisers etc.
- Thermocouple type K, T
- 10, 25, 50 & 100 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour code (cores & jacket) to IEC-584-3

Type	Conductors	Reel Length	Manufacturers Code	Order Code
K	1/0.315mm	10m	WK-300-D	XF-1651-FAR
K	1/0.315mm	25m	WK-300-D	XF-1649-FAR
K	1/0.315mm	50m	WK-300-D	XF-1650-FAR
K	1/0.315mm	100m	WK-300-D	XF-1652-FAR
Т	1/0.508mm	10m	WT-145-D	XF-1968-FAR
Т	1/0.508mm	25m	WT-145-D	XF-1254-FAR
Т	1/0.508mm	50m	WT-145-D	XF-1262-FAR
T	1/0.508mm	100m	WT-145-D	XF-1780-FAR