

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300621030](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower A-Size (7/8"-M22) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 14 AWG, Black TPE Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Cordsets
 Series [130062](#)
 Connector End A BradPower A-Size (7/8"-M22)
 Connector End B BradPower A-Size (7/8"-M22)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower A-Size
 Protocol FF
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78172550707

Physical

Cable Diameter 9.47mm (.373")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Black Epoxy Coated Zinc
 Material - Plating Mating Gold
 Net Weight 554.000/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -20° to +90°C
 Wire Size AWG 14
 Wire/Cable Type TC-ER

Electrical

Current - Maximum per Contact 15.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 114030K21M050G

Reference - Drawing Numbers

Sales Drawing SD-130062-023-001



EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Not Relevant

Not Reviewed

Not Contained

CER_4000383479_00_000.pdf

Search Parts in this Series

[130062 Series](#)

This document was generated on 10/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION