

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080520](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, Female (Straight) to Male RJ-45 (Straight), 22 AWG, Green Shielded TPU Cat5e Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
IP Rating	IP20, IP67
Material - Contact	Bronze
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Micro-Change (M12), RJ45
Region	America, Asia, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78172545841

Physical

Cable Diameter	6.80mm (.268")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Green
Coupling Style	Push and Latch, Threaded
Gender	Female-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	FPM
Material - Plating Mating	Gold
Net Weight	178.562/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-40° to +80°C
Wire Size AWG	22
Wire/Cable Type	Shielded TPU

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Material Info

Engineering Number	ERWPAU7012M020
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	1201088377-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410036_00_000.pdf

CER_4000410293_00_000.pdf

Search Parts in this Series

[120108 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION