

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300680110](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"-M35) Quick-Change Male to Micro-Change Female Pass Thru, 3-Pole

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Field Attachable / Accessories
 Series [130068](#)
 Approvals cULus Listed
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower D-Size
 Taxonomy Circular Industrial Connectors
 Type Reducer
 UPC 78172552013

Physical

Cable Diameter N/A
 Coupling Type External/Internal Thread
 Diagnostics / LEDs No
 Diagnostics Port No
 Gender Male-Female
 Keyway Single
 Material - Connector Body PVC
 Material - Coupling Nut Anodized Aluminum, Black Epoxy Coated Zinc
 Material - Plating Mating Gold
 Net Weight 548.000/g
 Orientation Straight
 Poles 3
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG N/A

Electrical

Current - Maximum per Contact 15.0A
 Voltage - Maximum 600V AC/DC

Material Info

Engineering Number 1C3030-001E

Reference - Drawing Numbers

Sales Drawing SD-130068-001-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130068 Series](#)