

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200680190](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 22 AWG PVC Cable, 1.0m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Tees and Splitters  
 Series [120068](#)  
 IP Rating IP67  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Taxonomy Industrial Tees and Splitters  
 Type Splitter - In-line  
 UPC 78678845021

**Physical**

Color - Cable Jacket Yellow  
 Drop Connector N/A  
 Drop Gender N/A  
 Keyway Single  
 LED Indicator No  
 Left Trunk Connector Micro-Change (M12)  
 Left Trunk Gender Male  
 Leg 1 Length 1.0m  
 Leg 2 Length 1.0m  
 Material - Cable Jacket TPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Nickel-plated Brass  
 Net Weight 232.828/g  
 Poles 3 Female/4 Male  
 Right Trunk Connector Micro-Change (M12)  
 Right Trunk Gender Female  
 Temperature Range - Operating -30°C TO +80°C

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 884A30K03M010

**Reference - Drawing Numbers**

Sales Drawing SD-120068-022-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000410546\_00\_000.pdf

**Search Parts in this Series**

[120068 Series](#)