

MPMP ARCA 5050



Sample image

Order symbol: MPMP ARCA 5050

Product nbr: 8120929

Description : Mounting plate
multi-perforated (450x450x2 mm -
ø3.6 mm)

Remarks : Galvanized steel. for size
500x500x210

Including :

EAN: 6418074314734

El. number:

- Finland:
- Denmark:
- Sweden:

Dimensions:

	Length	Width	Height
mm:		450	450
inch:			

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates: