

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300480237](#)

Status: **Active**

Overview:

Description: Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, Male (Straight) to Male RJ-45 (Straight), 26 AWG, Teal Shielded PVC Cat5e Cable, 5.0m (16.40') Length

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [130048](#)
 Connector End A Micro-Change (M12)
 Connector End B RJ-45 (standard)
 IP Rating IP20, IP67
 Material - Contact Brass, Phosphor Bronze
 Overview brad_industrial_ethernet_solutions
 Performance Category 5e
 Product Name Micro-Change (M12), RJ45
 Region America
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78172512530

Physical

Cable Diameter 5.70mm (.224")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Teal
 Coupling Style Push and Latch, Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Net Weight 254.865/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -25° to +75°C
 Wire Size AWG 26
 Wire/Cable Type Shielded PVC

Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V

Material Info

Engineering Number E16A06015M050

Reference - Drawing Numbers

Sales Drawing SD-130048-0237-001

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Contained Per -
 ED/30/2017 (7 July
 2017)
 Di-(2-ethylhexyl)phthalat

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130048](#) Series