

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300480248](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, Male (Straight) to Male RJ-45 (Straight), 24 AWG, Teal Unshielded PVC Cat5e Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [130048](#)
 Connector End A Micro-Change (M12)
 Connector End B RJ-45 (standard)
 IP Rating IP67
 Material - Contact Copper Alloy, Phosphor Bronze
 Overview [Brad Industrial Ethernet Solutions](#)
 Performance Category 5e
 Product Name Micro-Change (M12), RJ45
 Region America, Asia, Europe
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78172501147

Physical

Cable Diameter 6.35mm (.250")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Teal
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Net Weight 237.682/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -25° to +75°C
 Wire Size AWG 24
 Wire/Cable Type Unshielded PVC

Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 30V AC / 60V DC

Material Info

Engineering Number E16A06002M050

Reference - Drawing Numbers

Sales Drawing SD-130048-004-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410546_00_000.pdf

Search Parts in this Series

[130048 Series](#)

This document was generated on 10/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION