Twist-Lock[®] Devices 20A 3-Phase 480V AC, 3-Pole 4-Wire Spring Terminated Flanged Inlet

Features

- · Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

Ordering Information

DescriptionDevice ColorUPC NumberCatalog NumberNylon casing, back wired.White78358568168HBL2435ST

Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42

Specifications

Housing Nylon
Terminal Retainer Nylon
Plunger Nylon
Blades Copper Alloy
Terminal Spring Clamp Spring Steel
Assemby Screws Zinc Plated Tri-drive

Mounting Screw Nickel Plated Brass, 8- 32 Thread

Weight (lbs) 0.25

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated

current

Dielectric Voltage Withstands 3,000V minimum

Mechanical

Terminal Accommodation #14 AWG - #6 AWG solid or #14AWG - #8AWG

stranded copper wire

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C, Minimum -40°C

(w/o impact)

HUBBELL





Online Resources

eCatalog

