

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680250](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 0.60m Length, TPE Cable

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Tees and Splitters
 Series [120068](#)
 IP Rating IP67
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Taxonomy Industrial Tees and Splitters
 Type Splitter - In-line
 UPC 78678883488

Physical

Color - Cable Jacket Yellow
 Drop Connector N/A
 Drop Gender N/A
 Keyway Single
 LED Indicator No
 Left Trunk Connector Micro-Change (M12)
 Left Trunk Gender Male
 Leg 1 Length 0.30m
 Leg 2 Length 0.30m
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 93.893/g
 Poles 3 Female/4 Male
 Right Trunk Connector Micro-Change (M12)
 Right Trunk Gender Female
 Temperature Range - Operating -30°C to +70°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 884F30K05M05M03

Reference - Drawing Numbers

Sales Drawing SD-120068-028-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

EU RoHS	China RoHS
CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	50 Image
China ROHS	Not Relevant
ELV	Not Contained
RoHS Phthalates	CER_4000408918_00_000.pdf
ZZCERT_CE - Declaration of Conformity	
ZZCERT_UKCA - Declaration of Conformity	CER_4000410285_00_000.pdf

Search Parts in this Series

120068 Series