

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of GCG188L8EE105KA07# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=GCG188L8EE105KA07%23

"#" indicates a package specification code.




< List of part numbers with package codes > GCG188L8EE105KA07D GCG188L8EE105KA07J

GCG188L8EE105KA07D



Appearance & Shape







| Packaging | Specifications | Standard |
|-----------|------------------|----------|
| | | Packing |
| | | Quantity |
| D | 180mm Paper Tape | 4000 |
| J | 330mm Paper Tape | 10000 |

| Mass (typ.) | | |
|-------------|-------|--|
| 1 piece | 6.3mg | |
| φ180mm Reel | 144g | |



Derating4. Limited to Conductive Glue Mounting

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





GCG188L8EE105KA07D

Note: This datasheet may be out of date. Please download the latest datasheet of GCG188L8EE105KA07# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=GCG188L8EE105KA07%23

"#" indicates a package specification code.



Specifications

| Length | 1.6±0.2mm |
|--|----------------|
| Width | 0.8±0.1mm |
| Thickness | 0.8±0.1mm |
| Capacitance | 1.0µF ±10% |
| Distance between external terminals g | 0.5mm min. |
| External terminal size e | 0.2 to 0.5mm |
| Operating Temperature Range | -55°C to 150°C |
| Rated Voltage | 16Vdc |
| Size code in inch(mm) | 0603 (1608M) |
| Capacitance change rate | +15.0/-40.0% |
| Temperature characteristics (complied standard) | -(Murata) |
| Temperature range of temperature characteristics | -55℃ to 150℃ |

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

