


# GMA0D3R71A103MA01T

“#” indicates a package specification code.



< List of part numbers with package codes >  
GMA0D3R71A103MA01T

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
T	Bulk Tray	400

Mass (typ.)	
1 piece	0.38mg

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GMA0D3R71A103MA01T

“#” indicates a package specification code.

## Specifications

Length	0.38±0.05mm
Width	0.38±0.05mm
Thickness	0.3±0.05mm
Capacitance	10000pF ±20%
Operating Temperature Range	-55°C to 125°C
Rated Voltage	10Vdc
Size code in inch(mm)	015015 (038038M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X7R(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.