

Coaxial Panel Connector 23_SHV-50-0-1/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60498_MIL-STD-348A/314



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	0.3 GHz

Mechanical Data

Number of matings	500
Weight	0.0144 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00068551
Catalogue drawing	DCA-00010367
Mounting hole	DOU-00010585

Ordering Information

Single package	23_SHV-50-0-1/133_NE
----------------	----------------------