


Coaxial PCB Connector 85_MCX-50-0-16/111_N

Description

Right angle PCB jack

Interface Standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0017 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00012853
Catalogue drawing	DCA-00012855

Ordering Information

Tape and Reel package	85_MCX-50-0-16/111_NM
Bulk 100 pcs package	85_MCX-50-0-16/111_NH
Single package	85_MCX-50-0-16/111_NE

Remarks

PCB connector with stand-offs