

Coaxial Panel Connector 23_SK-50-0-51/199_N

Description

Straight panel receptacle jack, flange mount

Interface standards
MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz

Mechanical Data

Number of matings	500
Weight	0.0029 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Related Documents

Outline drawing	DOU-00010368
Catalogue drawing	DCA-00010370
Assembly instruction	DOC-0000187662
Mounting hole	DOU-00010365

Ordering Information

Single package	23_SK-50-0-51/199_NE
----------------	----------------------

Remarks

Hermetic sealed connector without glass bead supplement 73_Z-0-0-203 (1E-8 Torr l/s or cc/s at 1 atm), system leak rate dependent on customers process execution. For fixing hermetic seal while soldering, tool 74_Z-0-0-227 is recommended.