

EKDMAT05-KIT:

Power Inductors for DC-DC Converter Circuit for Automotive:

No.	QTY	MANUFACTURER'S PART NUMBER	Product Description	DESCRIPTION
1	10	DFE2HCAHR33MJ0L	Fixed IND SMD	Fixed IND 0.33uH 5.8A POWRTRN
2	10	DFE2HCAHR47MJ0L	Fixed IND SMD	Fixed IND 0.47uH 5.1A POWRTRN
3	10	DFE2HCAHR68MJ0L	Fixed IND SMD	Fixed IND 0.68uH 4.4A POWRTRN
4	10	DFE2HCAH1R0MJ0L	Fixed IND SMD	Fixed IND 1uH 3.4A POWRTRN
5	10	DFE2HCAH1R5MJ0L	Fixed IND SMD	Fixed IND 1.5uH 2.9A POWRTRN
6	10	DFE2HCAH2R2MJ0L	Fixed IND SMD	Fixed IND 2.2uH 2.5A POWRTRN
7	10	DFE2MCAHR15MJ0L	Fixed IND SMD	Fixed IND 0.15uH 6.1A POWRTRN
8	10	DFE2MCAHR24MJ0L	Fixed IND SMD	Fixed IND 0.24uH 5A POWRTRN
9	10	DFE2MCAHR33MJ0L	Fixed IND SMD	Fixed IND 0.33uH 4.2A POWRTRN
10	10	DFE2MCAHR47MJ0L	Fixed IND SMD	Fixed IND 0.47uH 3.6A POWRTRN
11	10	DFE2MCAH1R0MJ0L	Fixed IND SMD	Fixed IND 1uH 2.5A POWRTRN
12	10	DFE2MCAH1R5MJ0L	Fixed IND SMD	Fixed IND 1.5uH 2.1A POWRTRN
13	10	DFE2MCAH2R2MJ0L	Fixed IND SMD	Fixed IND 2.2uH 1.7A POWRTRN
14	10	LQM18PH1R0MFRL	Fixed IND SMD	Fixed IND 1uH 950mA POWRTRN
15	10	LQM18PH1R5MFRL	Fixed IND SMD	Fixed IND 1.5uH 800mA POWRTRN
16	10	LQM18PH2R2MFRL	Fixed IND SMD	Fixed IND 2.2uH 750mA POWRTRN
17	10	LQM18PH3R3MFRL	Fixed IND SMD	Fixed IND 3.3uH 700mA POWRTRN
18	10	LQM18PH4R7MFRL	Fixed IND SMD	Fixed IND 4.7uH 620mA POWRTRN
19	10	LQM21PHR47NG0D	Fixed IND SMD	Fixed IND 0.47uH 2700mA POWRTRN
20	10	LQM21PHR54NG0D	Fixed IND SMD	Fixed IND 0.54uH 2000mA POWRTRN
21	10	LQM21PH1R0NGCD	Fixed IND SMD	Fixed IND 1uH 1150mA POWRTRN
22	10	LQM21PH1R5NGCD	Fixed IND SMD	Fixed IND 1.5uH 1000mA POWRTRN
23	10	LQM21DH100M70L	Fixed IND SMD	Fixed IND 10uH 300mA POWRTRN
24	10	LQM21DH220M70L	Fixed IND SMD	Fixed IND 22uH 220mA POWRTRN
25	10	LQM21DH470M70L	Fixed IND SMD	Fixed IND 47uH 200mA POWRTRN
26	10	LQM21DH150M70L	Fixed IND SMD	Fixed IND 15uH 250mA POWRTRN
27	10	LQM21DH330M70L	Fixed IND SMD	Fixed IND 33uH 200mA POWRTRN
28	10	LQM21DH101M70L	Fixed IND SMD	Fixed IND 100uH 160mA POWRTRN
29	10	LQM18DH6R8M70L	Fixed IND SMD	Fixed IND 6.8uH 330mA POWRTRN
30	10	LQM18DH100M70L	Fixed IND SMD	Fixed IND 10uH 300mA POWRTRN
31	10	LQM18DH150M70L	Fixed IND SMD	Fixed IND 15uH 220mA POWRTRN
32	10	LQM18DH220M70L	Fixed IND SMD	Fixed IND 22uH 200mA POWRTRN
33	10	LQM18DH330M70L	Fixed IND SMD	Fixed IND 33uH 200mA POWRTRN
34	10	LQM18DH470M70L	Fixed IND SMD	Fixed IND 47uH 180mA POWRTRN