

## Coaxial Cable Connector 11\_TNC-50-4-23/12-\_N

### Description

Straight cable plug

Interface standards

IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



### Technical Data

#### Electrical Data

Impedance	50 Ω	
Interface frequency max.	11 GHz	
Frequency range	DC to 6 GHz	6 to 11 GHz
Return loss	25 dB	18 dB

#### Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.024 kg

#### Environmental Data

Operating temperature	-60 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00127638
Catalogue drawing	DCA-00129732
Assembly instruction	DOC-0000294172

### Ordering Information

Single package	11_TNC-50-4-23/12-_NE
----------------	-----------------------

### Additional Information

Suitable cables	EACON_4C
-----------------	----------