


## Coaxial PCB Connector 85\_SMB-50-0-1/111\_N

### Description

Right angle PCB jack

Interface Standards

IEC 60169-10\_MIL-STD-348A/311\_CECC 22130



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	4 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.0029 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00012763
Catalogue drawing	DCA-00012809

### Ordering Information

Single package	85_SMB-50-0-1/111_NE
Bulk 100 pcs package	85_SMB-50-0-1/111_NH

### Remarks

PCB connector with stand-offs