

Coaxial Panel Connector 23_QMA-50-0-2/111_N

Description

Straight panel receptacle plug, flange mount

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Number of matings 100
Weight 0.0023 kg

Environmental Data

Operating temperature -40 °C to 80 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00011474
Catalogue drawing DCA-00011476

Ordering Information

Bulk 100 pcs package 23_QMA-50-0-2/111_NH