

Coaxial Panel Connector 23_UHF-0-0-2/033_

Description

Straight panel receptacle jack, flange mount

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 0.2 GHz

Mechanical Data

Number of matings 500
Weight 0.0233 kg

Environmental Data

Operating temperature -55 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00010048
Catalogue drawing DCA-00198749

Ordering Information

Single package 23_UHF-0-0-2/033_-E