

Coaxial Cable Connector 11_SMB-50-2-41/111_N

Description

Straight cable plug

Interface standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 4 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0021 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Gold Plating (Nickel underplated) |
| Body | Brass | Gold Plating (Nickel underplated) |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | Gold Plating (without Nickel underplating) |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00006896 |
| Catalogue drawing | DOU-00006508 |
| Assembly instruction | DOC-0000179013 |

Ordering Information

| | |
|----------------------|-----------------------|
| Single package | 11_SMB-50-2-41/111_NE |
| Bulk 100 pcs package | 11_SMB-50-2-41/111_NH |

Additional Information

| | |
|-----------------|--|
| Suitable cables | K_02252_D, ENVIROFLEX_316_D, G_02232_D |
|-----------------|--|